

FIGURE AL-82 TUNED INPUT CHASSIS (INTERIOR VIEW)

Some capacitors may be connected to the coils. But they are connect to the switch as shown through the coils wire leads.

change to 1500pF


1500 pF

500pF

220pF

change to 270 pF

150pF



Take 1 Turn off = $2\frac{1}{2}$ Turn
10 METER COIL

Take 1 Turn off = $4\frac{1}{2}$ Turn
15 METER COIL

Take 2 Turns off = $7\frac{1}{2}$ Turn
20 METER COIL

Add another coax along with the old coax. (RG 178)

2000 pF

1300 pF

Change to 330 pF


Remove this cap

Change to 100 pF

Remove this cap

Center Panel of AL-82

Efficiency



Bottom View of Tube Chassis

